

Lab Supplies

Lens Care/Cleaning

Epoxies

Cables, Electrical


Safety & Blackout

Screws

19" Rack Hardware

Tools

Needle Nose Pliers




NP1

- Fine-Serrated Jaw for Good Clamping Grip
- Ideal for Gripping and Looping Wire
- Great for Tight Spaces

The NP1 is an essential electronics tool. With its fine-serrated jaw, the NP1 provides a good clamping grip and is ideal for gripping and looping wire. These needle nose pliers are best used in tight spaces.

ITEM#	\$	£	€	RMB	DESCRIPTION
NP1	\$ 36.40	£ 22.90	€ 33.90	¥ 347.60	Serrated Tip Needle Nose Pliers

4" Adjustable Wrench



AW4

- Great for Tight Spaces
- 0.53" Max. Extension
- Rugged Construction
- Quick One-Handed Adjustment
- Cushion Grip Handle

The AW4 is an ideal tool when small nuts or bolts need securing in tight spaces. With a maximum extension of 0.53", the AW4 is compatible with any nut and bolt from a #0 to a 5/16 thread.

ITEM#	\$	£	€	RMB	DESCRIPTION
AW4	\$ 24.00	£ 15.10	€ 22.30	¥ 229.20	4" Adjustable Wrench

Vise Grips



CG1

- Features a Quick-Release Lever
- Provide Sufficient Clamping Force
- Durable Stainless Steel

Powerful, double-lever action and a pressure-adjusting screw in the handle lock the jaws with a vise-like grip. Tools stay clamped on your work, leaving your hands free. To open the jaws, press the quick-release lever on the lower handle. All are made of heat-treated, nickel-plated alloy steel. Jaws are serrated.

ITEM#	\$	£	€	RMB	DESCRIPTION
CG1	\$ 19.70	£ 12.40	€ 18.30	¥ 188.10	Vise Grips

Wire Cutters



MPC1

These cutters are designed for cutting soft wire up to 20AWG. Although mainly aimed at electrical wires, the tool is perfectly suited for cutting optical fiber to length (but does not replace an actual cleaving tool, see XL410 or S90W)

- Low-Profile General Purpose Cutter
- Superior Blade Bypass Shear Cutting Action
- Greatly Reduces Mechanical Shock
- Flush Cuts Soft Wire up to 20AWG

ITEM#	\$	£	€	RMB	DESCRIPTION
MPC1	\$ 10.30	£ 6.50	€ 9.60	¥ 98.40	Multi-Purpose Wire Cutters

Wire Strippers



WS10

WS16

- Ideal for Cutting, Stripping, and Looping Wire
- Spring-Loaded for Self-Opening

WS16-Red Handle

- Strips Wire Between 16AWG and 26AWG (1.0 to 0.14mm²)

WS10-Yellow Handle

- Strips Wire Between 10AWG and 18AWG (4.0 to 0.75mm²)

Wire strippers provide a safe way of removing the outer layers of wires and cables. A series of slots with different gap sizes ensures that the inner wire or fiber isn't damaged. Although designed for electrical wires, the tool is well suited for stripping the jacket and furcation tubing off fibers.

ITEM#	\$	£	€	RMB	DESCRIPTION
WS10	\$ 20.50	£ 12.90	€ 19.10	¥ 195.80	10 AWG-18 AWG Wire Strippers
WS16	\$ 20.50	£ 12.90	€ 19.10	¥ 195.80	16 AWG-26 AWG Wire Strippers