

# LASER OPTICAL DENSITY CERTIFICATION

## I AB5

Supplier: Thorlabs Limited  
Purchase Order Number: EO-265946  
Requirements: EN 12254: 2010(E), Paragraph 5.3 Resistance to Laser Radiation, Table 2.  
180-315 nm Range.

Cert. Number: 51492  
Date: September 30, 2015

### TEST PARAMETERS

Coating Type: N/A	Substrate Material: Fabric
Test Wavelength: 266 nm	Incidence Angle: 0°
Polarization: Random	PRF : 10 Hz
Pulsewidth (FWHM): 45 ms	Transverse Mode : TEM <sub>00</sub>
Spot Diameter (1/e): 0.297 mm	Axial Modes: Multiple
Test Prep: N <sub>2</sub> blow	Number of Sites: 1
Quantity: 3	Exposure Duration: 100 seconds

### TEST RESULTS:

<u>Sample</u>	<u>Measurement Level</u>
6	Sample maintains AB5 during irradiation.
6	Sample maintains AB5 during irradiation.
6	Sample maintains AB5 during irradiation.

COMMENTS: None.

**Spica Technologies certifies that this sample has been exposed to the parameters described above. All test and calibration data are maintained on file. All instrument calibration is traceable to NIST.**

Test conducted by \_\_\_\_\_

  
**Spica**  
Technologies Inc.

18 Clinton Drive #3  
Hollis, NH 03049  
[www.spicatech.com](http://www.spicatech.com)  
603-882-8233